



Liquidtight Flexible Cord & Cable Fittings

T&B Catalog Number:

2932SST

UPC Number:

78620987799

Status:

Active

Description:

Liquidtight Strain Relief Connector, 3/4 Inch, Straight, Cord Range 0.500 to 0.750 Inch, 304 Stainless Steel Body with Rubber Bushing

Features

Type 304 stainless steel construction for your harshest environments

Ranger liquidtight cord connectors offer twice the cord diameter range of similar connectors, so you can do more with fewer sizes to order and stock.

Ranger connectors form a non-slip mechanical grip, providing a liquidtight seal and the strain relief required for flexible portable cord connections.

Superior corrosion resistance in wash down areas and other corrosive environments.

Stands up to heat and UV exposure better than non-metallic connectors.

Beveled, moisture and oil-resistant synthetic rubber bushing system ensures superior compression and sealing of fitting to cord.

Bushing marked with cord range for easy identification out of box.

Application

Ideal for MRO and OEM applications in corrosive environments such as food & beverage and pharmaceutical processing wash down area.

Pulp and paper mills, wastewater treatment, saltwater applications and petrochemical refining.

General

Material

Stainless Steel

Cord and Cable Types

SJ, SJE, SJEO, SJEOO, SJO, SJOW, SJOO, SJOOW, SJT, SJTW, SJTO, SJTOW, SJTOO, SJTOOW, SO, SOW, SOO, SOOW, SV, ST, STD, SVD.

Dimension Information

Hub Size (inches)

3/4

Dimension A (inches)

2.063

Dimension B (inches)

0.630

Dimension C (inches)

1.125

Cord Range (inches)

.500 - .750

Specifications

3dmodel

Available on Website

Temperature Rating

-20 C to 105 C

Packaging

T&B Inner Pack

10

Package in Units

50

T&B Sold in UOM

Each

T&B Weight Per UOM

20.5 lbs. per 100

Application Support

304 Stainless Steel Corrosion Compatibility Chart - Available on Website

T&B Sales Drawings

wsd-000335

Product Overview

Available on Website

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:

E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com