



**Liquidtight Flexible Cord & Cable Fittings**

**T&B Catalog Number:**

2941NM

**UPC Number:**

78621079747

**Status:**

Active

**Description:**

Liquidtight Strain Relief Connector, Straight, 1 Inch NPT Thread, Cable Range 0.500 Inch/12.7mm to 0.750 Inch/19.0mm, IP65 Rating, UV Resistant Polyamide 6.6 Body, Black

**Features**

- Extended range with superior strain relief.
- Reduced overall size, fits into tighter spaces.
- Gland nut designed to restrict cable bending.

**Application**

- Provide a means for passing a cord cable into an enclosure through a bulkhead
- Suitable for Ordinary, Wet or Dry locations.

**General**

Material	Nylon
Cord and Cable Types	S, SO, SV, ST, STD, SJ, SJO, SJT, SJTO, SVD

**Dimension Information**

Hub Size (inches)	1
Dimension A (inches)	1 13/32
Dimension B (inches)	2 11/32
Dimension C (inches)	25/32
Cord Range (inches)	.500-.750
Throat Diameter (inches)	0.98

**Specifications**

3dmodel	Available on Website
---------	----------------------

**Packaging**

T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	9.38 lbs. per 100

**Application Support**

T&B Instruction Sheets	ta00927-tb2
Product Overview	Available on Website
Specifications	Available on Website
Portable Cord Selection Table	Available on Website

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**



File Nbr:  
E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)