

Splice Connector T&B Catalog Number:

2RF4

UPC Number:

78621089467

Status:

Active

Description:

Nylon-Insulated Butt Splice, Length 1.85 Inches, Width .52 Inches, Maximum Insulation Diameter .510, Wire Range #4, Color Blue, Copper, Tin Plated



Features

Nylon insulated splices meet or exceed the requirements of MIL-T-7928. These splices are color-coded according to wire size.

General



Insulation Type	Insulated Nylon
Terminal Series	RF
Material	Copper
Finish	Electro -Tin Plated
Color	Yellow
Wire Range	4

Dimension Information

Maximum Insulation (inches)	.510
Stock Thickness	.04
A (inches)	1.85
B (inches)	.52

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

Tooling

Tool Charts	Available on Website
Application Tools	TBM6, TBM6S
Recommended Tool	TBM6S

Packaging

T&B Order Multiple	15
T&B Inner Pack	15
Package in Units	150
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	2.81 lbs. per 100

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com