



## Rigid/IMC Conduit Fittings

### T&B Catalog Number:

373

### UPC Number:

78621000373

### Status:

Active

### Description:

1-1/4 Inch Hub Connector, Malleable Iron Electro Zinc Plated, Nylon Insulated for Use with Rigid/IMC Conduit

### Features

Rugged steel/malleable iron construction
Tapered internal threads for water-tight/dust-tight union
Threads relieved to prevent bottoming of conduit, ensuring sound assembly
Recessed sealing ring at box end; sealing ring captivated
Hardened steel/malleable iron/copper-free aluminum locknuts designed to provide high quality ground continuity; extended reach of locknut permits clamping on thin boxes and enclosures
Insulated throat, insulates conductors, prevents abrasion and thinning of conductor insulation, reduces wire pull effort

### Application

To connect threaded metal conduit (ferrous rigid/non-ferrous rigid/PVC coated/or intermediate metal) to a threadless opening in a box or enclosure in outdoor or indoor location exposed to continuous or intermittent moisture.
To positively bond conduit to box or enclosure.
Suitable for hazardous locations use in Class I, Division 2; Class II, Division 1&2; Class III, Division 1 & 2 per NEC 501-4(b); 502-4 (a) and 503-3 (a).
Suitable for hazardous locations use in Class II, Groups E, F, G & Class III locations per CEC 18-202; 18-252; 18-302; 18-352.
When used with neoprene O-ring, provides water-tight threaded hub on enclosures
UL Listed 105 degree C

### General

Trade Size (inches)	1-1/4
Material	Malleable Iron
Finish	Electro Zinc Plated

### Dimension Information

Dimension A (inches)	2 9/16
Dimension B (inches)	1 5/8
Dimension C (inches)	1

### Specifications

3dmodel	Available on Website
---------	----------------------

### Packaging

T&B Inner Pack	5
Package in Units	25

T&B Sold in UOM	Each
T&B Weight Per UOM	56.81 lbs. per 100

### Application Support

Spacing Chart Available on Website

### Notes

Availabe with DURA-PLATE Finish

### Certifications

RoHS Compliance Yes

### Certifications



File Nbr:

E 23018

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com