



Rigid/IMC Conduit Fittings

T&B Catalog Number:

376

UPC Number:

78621000376

Status:

Active

Description:

2-1/2 Inch Hub Connector, Malleable Iron Electro Zinc Plated, Nylon Insulated for Use with Rigid/IMC Conduit

Features

| |
|---|
| Rugged steel/malleable iron construction |
| Tapered internal threads for water-tight/dust-tight union |
| Threads relieved to prevent bottoming of conduit, ensuring sound assembly |
| Recessed sealing ring at box end; sealing ring captivated |
| Hardened steel/malleable iron/copper-free aluminum locknuts designed to provide high quality ground continuity; extended reach of locknut permits clamping on thin boxes and enclosures |
| Insulated throat, insulates conductors, prevents abrasion and thinning of conductor insulation, reduces wire pull effort |

Application

| |
|--|
| To connect threaded metal conduit (ferrous rigid/non-ferrous rigid/PVC coated/or intermediate metal) to a threadless opening in a box or enclosure in outdoor or indoor location exposed to continuous or intermittent moisture. |
| To positively bond conduit to box or enclosure. |
| Suitable for hazardous locations use in Class I, Division 2; Class II, Division 1&2; Class III, Division 1 & 2 per NEC 501-4(b); 502-4 (a) and 503-3 (a). |
| Suitable for hazardous locations use in Class II, Groups E, F, G & Class III locations per CEC 18-202; 18-252; 18-302; 18-352. |
| When used with neoprene O-ring, provides water-tight threaded hub on enclosures |
| UL Listed 105 degree C |

General

| | |
|---------------------|---------------------|
| Trade Size (inches) | 2-1/2 |
| Material | Malleable Iron |
| Finish | Electro Zinc Plated |

Dimension Information

| | |
|----------------------|-------|
| Dimension A (inches) | 4 1/8 |
| Dimension B (inches) | 1 7/8 |
| Dimension C (inches) | 1 1/8 |

Specifications

| | |
|---------|----------------------|
| 3dmodel | Available on Website |
|---------|----------------------|

Packaging

| | |
|------------------|---|
| T&B Inner Pack | 1 |
| Package in Units | 5 |

| | |
|--------------------|------------------|
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 186 lbs. per 100 |

Application Support

Spacing Chart Available on Website

Notes

Availabe with DURA-PLATE Finish

Certifications

RoHS Compliance Yes

Certifications



File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com