



Representative

**Catalog Number:** **BG100-14-4**  
**Product ID:** 7TAD013050R0003  
**UPC Number:** 78621016157  
**Status:** Active

1 Inch Blackjacket Grounding Bushing, Malleable Iron Zinc Plated, Wire Range 14 4 for Use with Threaded or Threadless Rigid/IMC Conduit

#### Header

3D Model Available on Website

#### UNSPSC Specifications

UNSPSC	39121312 Electrical bushing
IGCC	4442 Electrical bushing
Brand Name	T&B
Type	Grounding Bushings & Accessories
Application	For Use with Rigid/IMC Conduit
Standard	UL E3060, CSA
Size	1-Inch
Material	Malleable Iron

#### Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x5x4
Outer Quantity	50
Outer Dimensions (inches)	8.3x5.5x8.3
Weight Uom	22 lbs. per 100

#### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com