



T&B®

Rigid/IMC Conduit Fittings T&B Catalog Number:

UPC Number: H125CAP
78621004479
Status: Active
Description:

1-1/4 Inch Zinc Capoff with Thermoplastic Insulating Throat, Sealing Ring Nitrile (BUNA-N) for Use with Rigid/IMC Conduit

Application

CSA Certified for hazardous locations Class II Groups E.F.G. Class III.
Meets NEMA sealing requirements for NEMA 3R, 4 & 13 enclosures.

General

Trade Size (inches) 1-1/4
Material Zinc

Dimension Information

Diameter (inches) 2 3/8
Height (inches) 1 25/32
Dimension A (inches) 23/32
Dimension B (inches) 1 21/32
Dimension C (inches) 1/4

Specifications

3dmodel Available on Website

Packaging

T&B Inner Pack 5
Package in Units 25
T&B Sold in UOM Each
T&B Weight Per UOM 48 lbs. per 100

Application Support

Spacing Chart Available on Website

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com