



Flexible Conduits & Fittings

T&B Catalog Number:

LLPA-10A.50

UPC Number:

78620995764

Status:

Active

Description:

Fine profile medium-wall very flexible black conduit. (LLPA) Material - polyamide 6, conduit size NW - 10.

Application

Machine

Renewable Energy

Technology

Characteristics

Good impact resistance also at low temperatures and dry conditions

Self-extinguishing

Free from halogens and cadmium

Good flexibility

General

Material Polyamide 6

Material-Conduit Core Non-Metallic

Color Black

System Smart Line

Compatible With PMA Smart Line, PMAFIX Pro, PMAFIX, PMAGRIP

Dimension Information

Conduit Size (inches) 5/16

Conduit Size NW (mm) 10

Conduit Size Metric (mm) 12

Inside Diameter (inches) 0.38

Outside Diameter (inches) 0.51

Inside Diameter (mm) 9.6

Outside Diameter (mm) 13

Static Radius (mm) 20

Rec. Fitting Thread-Metric M12 x 1.5

Rec. Fitting Thread-PG 9

Technical Information

Temperature Range-Continuous (Celsius) -40 to +105

Temperature-Short-Term (Celsius) 140

Fatigue Life High

Technical Data Sheet Available on Website

Chemical Resistance Chart Available on Website

Packaging

T&B Order Multiple 1

T&B Inner Pack 1

Package in Units 20

T&B Sold in UOM Each

T&B Weight Per UOM 3.3 lbs. Each

Application Support

PMA Reference Guide Available on Website

Conduit Guide-Smart Line Available on Website

Product Overview-Smart Line Conduits Available on Website

Product Overview-Smart Line Connectors Available on Website

Product Overview-System Supports Available on Website

Certifications

RoHS Compliance Yes

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com