



## Type B Liquidtight Tubing & Fittings

### T&B Catalog Number:

LTC038GY

**UPC Number:**

78621088075

**Status:**

Active

**Description:**

3/8 Inch Gray Non-metallic Type B Commercial Grade Liquidtight Conduit

### Features

Fast installation, even in tight or cramped spaces.

Smooth inner diameter allows easy wire pulling.

Smooth outer jacket uses material approved for outdoor use, is sunlight resistant and oil resistant.

Lightweight and liquidtight.

### Application

UL Listed for direct burial

### General

Material

PVC

Color

Gray

Working Temperatures

-18 C to +105 C

### Dimension Information

Size (inches)

3/8

I.D. - Minimum (inches)

0.484

I.D. - Maximum (inches)

0.504

O.D. - Minimum (inches)

0.69

O.D. - Maximum (inches)

0.71

### Packaging

T&B Order Multiple

100

Package in Units

100

T&B Sold in UOM

Feet

T&B Weight Per UOM

12.69 lbs. per 100

### Application Support

MSDS Number

msds-0023-tb2

Guide to Nonmetallic Conduit Applications Available on Website

XTRAFLEX System Specifications

Available on Website

### Certifications

RoHS Compliance

Yes

### Certifications



File Nbr:

E 95745

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com