



C Series 35 A 600 VAC

6 or 12 Contacts + Ground

Install to Matching Series Hood/Base

6	12
	

Screw Terminal Contact Carrier Blocs de connexion

Screw Terminal Contact Carrier Blocs de connexion		6 + G	12 + G
 Male – Pins 20–10 AWG (0.5–6 mm ²)		MS206C	MS206C (1–6) + MS212C (7–12)
 Female – Sleeves 20–10 AWG (0.5–6 mm ²)		FS106C	FS106C (1–6) + FS112C (7–12)

				# of Contacts + Ground Connection		
Bases — Standard Mount				6	12	
Single Lever	Double Lever	Housing	NPT Entry (in.)	Lever Locking Type		
				Single	Double	Double
		Panel Base (No Cover)		PB316	PB116E	PB132
		Panel Base w/Cover		PB416		
		Box Base (No Cover)	1 x 3/4	BB416mv*	BB016Emv*	
			1 x 1	BB416H100mv	BB016EH100mv	BB032mv
			2 x 3/4	BB516mv*	BB116Emv*	
			2 x 1	BB516H100mv	BB116EH100mv	BB132mv
		Box Base w/Cover	1 x 1/2	BB616mv*†		
			1 x 1	BB616H100mv†		
			2 x 1/2	BB716mv*†		
			2 x 1	BB716H100mv†		
Hoods — Standard Mount						
		Side Entry	1 x 3/4	SH616mv‡	SH016mv‡	SH032mv
			1 x 1	SH716Hmv	SH116Hmv	SH132mv
			1x 1-1/4			SH132125mv
		Top Entry	1 x 3/4	TH816mv‡	TH216mv‡	TH232mv
			1 x 1	TH816H100mv	TH316Hmv	TH332mv
			1x 1-1/4			TH332125mv
Coupler Hoods — Inline For inline, portable or special service connections. Coupler Hoods mate to Standard Hoods ONLY.						
		Top Entry	1 x 3/4	CH816Hmv	CH616EHmv	CH632mv
			1 x 1	CH916Hmv	CH716EHmv	CH732mv
Lever Hoods — Reverse Locking Lever Hoods mate to Post Bases ONLY						
		Side Entry w/Lever(s)	1 x 3/4		LH016Emv*	
			1 x 1		LH116EHmv	
		Top Entry w/Lever(s)	1 x 3/4		LH216E*	
			1 x 1		LH316EHmv	
Bases — with Access Cover Post Bases accept Lever Hoods ONLY						
		Panel Base w/Posts + Cover			PB216†	
		Box Base w/Posts + Cover	1 x 3/4		BB216mv*†	
			1 x 1		BB216H100mv†	
			2 x 3/4		BB316mv*†	
			2 x 1		BB316H100mv†	

* High "H" profile may be available. Contact your Thomas & Betts sales representative.
 ** Low "L" profile may be available. Contact your Thomas & Betts sales representative.
 † Metal "M" cover may be available. Contact your Thomas & Betts sales representative.
 ‡ High "H" and Low "L" profile may be available. Contact your Thomas & Betts sales representative.