


Safety, Reusable and Double-Loop Cable Ties

Ideal for precision bundling!

Low-Profile All-Nylon 6.6 Ties

This fastener design from Thomas & Betts is ideal for use where clearance is a necessity and allows for easy pull-through in bulkheads and other tight spaces. Our contoured head eliminates snagging, and sharp edges are reduced by our safeguard walls.




Low-profile contoured head compared with the profile of a common cable tie.

- Low-profile, contoured head reduces clearance required for the bundle and enhances the appearance of your harness
- The safeguard wall eliminates exposure to sharp edges
- The saddleback fits snug against the contour of the wiring harness
- Sizes and colors available to accommodate varying requirements

STD. PKG. CAT. NO.	BULK PKG. CAT. NO.	MATERIAL	BUNDLE RANGE DIA. IN./MM	TENSILE STRENGTH LBS./N	TIE LENGTH IN./MM	STRAP WIDTH IN./MM	STRAP THICK IN./MM	STD. PKG. QTY.	BULK. PKG. QTY.
—	SF100-18	Natural	.13/3.3–1.00/25.4	18/80.07	4.65/118.11	.095/2.41	.04/1.09	—	1,000
SF100-18X-100	SF100-18X	UV Black	.13/3.3–1.00/25.4	18/80.07	4.65/118.11	.095/2.41	.04/1.09	100	1,000
—	SF200-18	Natural	.13/3.3–2.00/50.8	18/80.07	8.10/205.74	.1/2.41	.04/1.09	—	1,000
—	SF200-18X	UV Black	.13/3.3–2.00/50.8	18/80.07	8.10/205.74	.1/2.41	.04/1.09	—	1,000
—	SF175-50	Natural	.19/4.8–1.75/44.45	50/222.4	7.70/195.58	.19/4.75	.05/1.22	—	1,000
—	SF175-50X	UV Black	.19/4.8–1.75/44.45	50/222.4	7.70/195.58	.19/4.75	.05/1.22	—	1,000
—	SF175-50FR	Flame Retardant	.19/4.8–1.75/44.45	50/222.4	7.70/195.58	.19/4.75	.05/1.22	—	1,000
—	SF300-50X	UV Black	.19/4.8–3.00/76.2	50/222.4	11.33/287.78	.19/4.75	.05/1.22	—	1,000
—	SF400-50	Natural	.19/4.8–4.00/101.6	50/222.4	14.53/369.06	.19/4.75	.05/1.22	—	1,000
—	SF400-120X	UV Black	.38/9.6–4.00/101.6	120/533.8	14.58/370.33	.30/7.62	.07/1.78	—	500

Use these ties again and again!

Ty-Rap® Reusable Ties



STD. PKG. CAT. NO.	BODY WIDTH IN./MM	LENGTH IN./MM	BUNDLE DIA. IN./MM	TENSILE STRENGTH LBS./N	STD. PKG. QTY.
TYR505	.18/4.57	7.50/190.50	1.75/1.75	50/222.40	100
TYR508	.18/4.57	14.30/363.22	4.00/101.60	50/222.40	100


For use in temperatures ranging from -40° F to 185° F (-40° C to 85° C).

- Natural nylon color

Double Loop 6.6 Nylon Tie

Advantages:

- Enables parallel routing of two cable bundles with one single cable tie!
- Halogen- and silicone-free to meet your application needs
- Quick and easy pull-through increases productivity, reduces operator fatigue



BULK PKG. CAT. NO.	LENGTH IN./MM	WIDTH IN./MM	BUNDLE DIAMETER RANGE		TENSILE STRENGTH (LB/N)	INSTALLATION TOOLING FOR ALL SIZES	BULK PKG.
			LOOP 1 IN./MM	LOOP 2 IN./MM			
TB-12-50RLDH	11.8/299.72	.19/4.83	.1/2.54–2.8/71.12	.1/2.54–2.7/68.58	50/222.4	ERG50	1,000

- Natural nylon color

For use in temperatures ranging from -40° F to 185° F (-40° C to 85° C).