



Metal Clad Cable Termination Fittings & Accessories

T&B Catalog Number:

ST050-466

UPC Number:

78621071285

Status:

Active

Description:

Star Teck aluminum jacketed cable fitting hub size 1/2 inch Range over jacket 0.825-0.985 inches.

Features

Easy Installation-Exclusive power-grip. Provides a grip that's high up on the cable-not on the first convolution-so strip length and cutting of cable are not critical.

Dependable Service-stainless steel retaining ring. Withstands corrosive environments. Non-magnetic.

Dependable Grounding-Power-Grip grounding ring is non-magnetic stainless steel. Provides 360°; long-term dependable grounding. It makes immediate contact with the cable.

Watertight-Tapered bushing. Cone shaped to provide a secure, tight fit while eliminating cupping or water in vertical installations.

Easy to Install In Tight Spaces-Low profile glad nut fits tight spaces. Has grooves for screwdriver installation, and flats for a wrench. Durable and reusable with funnel entry for easy cable insertion.

Application

Provides means for passing armored, metal clad, jacketed cable through a bulkhead or enclosure in hazardous areas. (these fittings are suitable for hazardous areas when used with T&B sealing compound).

Form a mechanical grip and water and/or oil-resistant termination.

Provide grounding continuity of cable armor.

General

Material Aluminum

Dimension Information

Hub Size (inches)	1/2
Dimension A (inches)	0.612
Dimension B (inches)	2.133
Dimension C (inches)	1.633
Range Over Jacket -Minimum (inches)	0.825
Range Over Jacket -Maximum (inches)	0.985
Range Over Armor -Minimum (inches)	0.715
Range Over Armor -Maximum (inches)	0.905

Specifications

3dmodel Available on Website

Packaging

Package in Units	20
T&B Sold in UOM	Each
T&B Weight Per UOM	19.7 lbs. per 100

Application Support

T&B Instruction Sheets	ta00904-tb2
Product Specifications & Overview	Available on Website

Notes

*Note 1/2" Fittings do not have a removable armor stop.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E 38947

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com