



T&B[®]

Rigid/IMC Conduit Fittings T&B Catalog Number:

UPC Number: XJG84-TB
78621088112
Status: Active
Description:

3 Inch XJG Conduit Expansion Coupling with Internal Bonding Jumper, Body Malleable Iron Zinc Plated, Internal Bonding Jumper Tinned Copper Braid, Packing PTFE/Synthetic Fiber Material, 4 Inch Movement

Features

- No disassembly necessary to install. Fast, simple, and requires fewer steps.
- True Internal Bonding Jumper-no external grounding strap required, tamper-proof internal jumper protected from the environment.
- Exceeds code requirements for long conduit runs to permit linear movement.

Application

Allows for the contraction and expansion of a conduit run without reducing the mechanical or bonding integrity of the raceway.

General

Trade Size (inches)	3
Material	Malleable Iron
Finish	Zinc Plated

Dimension Information

Dimension A (inches)	4.96
B-Length (inches)	12.12
C-Height (inches)	5.25
Movement (inches)	4

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	14.67 lbs. Each

Application Support

T&B Instruction Sheets	ta02289-tb2
------------------------	-------------

Certifications

RoHS Compliance	No
-----------------	----

Certifications



File Nbr:
E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com