

T&B Conduit Fittings

Liquidtight Flexible Metal Conduit Fittings



NEMA 3R, 4, 6 & 13
 Temperature range — -30°C to 105°C.

Liquidtight K.O. Plugs



Cat. No.	Size	Dimensions (in.)
		A
5710	1/2"	1-9/32"
5711	3/4"	1-1/2"
5712	1"	1-27/32"
5713	1-1/4"	27/32"
5714	1-1/2"	2-1/2"
5715	2"	3-3/32"
5716	2-1/2"	3-21/32"
5717	3"	4-19/64"
5718	4"	5-19/64"

U.L. Listed liquidtight
 CSA not applicable
 Meets Coast Guard Regulation CG293