

Outdoor XTRA FLEX® Raceway System (Type B)



Specifications

- Color: Gray
- Length: 100 ft. for LTC038GY thru LTC125GY
50 ft. for LTC150GY and LTC200GY
- UL Temperature Rating:
80° C dry, 60° C wet
70° C oil. res. sunlight resistant,
outdoor, direct burial
- CSA Certified: File LR 80349-2
- CSA Temperature Rating: -18°C to 75°C
- Material: PVC Helix reinforcement surrounded
with flexible PVC
- Voltage Rating: 600V

CAT. NO. SERIES	TRADE SIZE (IN.)	I.D. (IN.)		O.D. (IN.)		STD. CTN.
		MIN.	MAX.	MIN.	MAX.	
LTC038GY	3/8	.484	.504	.690	.710	100
LTC050GY	1/2	.622	.642	.820	.840	100
LTC075GY	3/4	.820	.840	1.030	1.050	100
LTC100GY	1	1.041	1.066	1.290	1.315	100
LTC125GY	1 1/4	1.380	1.410	1.630	1.660	100
LTC150GY	1 1/2	1.575	1.600	1.865	1.900	50
LTC200GY	2	2.020	2.045	2.340	2.375	50

UL Listed: File E95745.

For use with Thomas & Betts LT38P, LT38M, LT500 series
and Liquidtight Flexible Metal Conduit Fittings.

Liquidtight Whip Assembly



CAT. NO.	CONDUIT SIZE (IN.)	LENGTH (FT.)	WIRE GAUGE	STD. CTN.
LTHWIP 12-6-10	1/2	6	#10	6
LTHWIP 12-4-10	1/2	4	#10	6
LTHWIP 34-6-8	3/4	6	#8	6
LTHWIP 34-4-8	3/4	4	#8	6

Whip with Metallic Fittings — One Straight, One 90°

LTWM 12-6-10	1/2	6	#10	6
LTWM 12-4-10	1/2	4	#10	6
LTWM 34-6-8	3/4	6	#8	6
LTWM 34-4-8	3/4	4	#8	6

Conduit Cutter



For Non-Metallic Flexible Conduit

CAT. NO.	DESCRIPTION
XF-CUT	For Cutting Non-Metallic Flexible Conduit up to 1"
XF-BLADE	Replacement Blade for XF-CUT