

PRODUCTS
[LCD Monitors](#)

- [Field Monitors](#)
- [4" - 6" Monitors](#)
- [7" - 20" Monitors](#)
- [23" - 70" Monitors](#)
- [Commercial Grade TV's](#)
- [Flush Mount Monitors](#)
- [Mobile Device](#)
- [Specialty Monitors](#)
- [Rack Mount Monitors](#)
- [Ceiling Mount Monitors](#)
- [Counter Mount Monitors](#)
- [Special Order Items](#)
- [3G-SDI Monitors](#)

[Accessories and Brackets](#)

CATALOG

- [Download](#)
- [Send Print Version](#)
- [Contact Us](#)

WHERE TO BUY

- [Dealers \(for customers\)](#)
- [Distributors \(for trade\)](#)

NEWSLETTER SIGNUP

Email Address

First Name

Last Name

Business Name

Interests

LCD-565
[Add to Wishlist](#) | [Add to Compare](#) | [Download as PDF](#)
PRODUCT DESCRIPTION

LCD-565 only: BNC IN/OUT jacks located on top for easy access (with self-termination feature)

LED backlight provides longer life, uses less power and provides better color saturation

Battery pack for field monitor use included

Ideal for troubleshooting system setup/fault location

Switch for Auto/Manual color adjustment

Low power consumption

Case made of durable ABS plastic

Manual controls for tint, color, brightness (and audio volume for LCD-562)

Battery pack provides approximately 5 ~ 6 hrs operation

Snap-on battery pack holds 8AA or 10 NiCad rechargeable batteries (batteries not included)

LCD-562KIT: 5.6" field kit with audio (no bnc in/out) with clip-on battery pack,

tote bag, and AC adaptor

LCD-565KIT: 5.6" field kit with bnc in/out with clip-on battery pack, tote bag, and AC adaptor

Response Time: 60ns/60ns (Rising/Falling)

ADDITIONAL INFORMATION

SKU:	LCD-565
Size	5.6"
GSA	Yes
Mount Type	Desk/Wall/Hot Shoe/Bracket
Resolution	960(H) x 234(V) dots
Brightness	200 cd/m squared (Nit)
Contrast	300:1
Display	5.6" a-Si TFT LCD
Back Light	LED
Input Signal	NTSC/PAL auto match
Pixels	224,640 Dots
Dot Pitch	.188mm(H) x .362mm(V)
Pixel Configuration	RGB Stripe
Viewing Angle	65/65/45/65
Video Input Signal Level	1.0V p-p (positive) 75 Ohm
Actual Visible Screen Size	(WH) 113.3 x 85mm / 85mm / 4.5" x 3.3"
Operating Temp	10-104 degrees F / 12-40 degrees C
Storage Temp	-13-140 degrees F / -25-60 degrees C
Power Requirements	11VDC-14VDC, 500 ma @ 12VDC
Power Consumption	4.0W (340ma @ DC 12V
Terminal Connections	BNC video IN/OUT (female) jacks 2.1mm DC IN jack
Weight	Net: 400 g / 14.0 oz. Gross: 0.6kg/1.3 lbs

[Compare Products](#)

You have no items to compare.