



Representative

**Catalog Number:** PAC345  
**Product ID:** 7TAA267200R0027  
**UPC Number:** 78378633014  
**Status:** Active

Aluminum Type PAC - Aluminum Parallel Groove Clamp with Cast Copper Liner for Wire  
 Range Main: 1/0-8 ASCR 1/0 Str.-8 Sol. AL/CU, Tap: ASCR 1/0 Str.-8 Sol. ALCU

### North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Parallel-Groove Clamp
Special Features	Most Corrosion-Resistant Groove Clamp Ever. Pressure-Cast Aluminum Body Effectively Seals Out Moisture and Resists Corrosion. Clamp Separates Conductors to Reduce the Possibility of Galvanic Corrosion.
Application	Securing Conductors
Size	Height 2-7/32 X Length 1-18/32 X Width 1-1/4 inch
Connection	Bolted
Conductor Range	Main: 1/0-8 ASCR 1/0 Str.-8 Sol. AL/CU, Tap: ASCR 1/0 Str.-8 Sol. ALCU
Number Of Conductors	2
Material	Aluminum
Insulation	None
Mounting	None
Environmental Conditions	All Seasons / Conditions

### Packaging

Inner Dimensions (inches)	xx
Outer Quantity	50
Outer Dimensions (inches)	8.1x7.4x6.7
Weight Uom	20.5 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com