



A Division of Troy-CSL Lighting, Inc.

MACH 120®

Project _____

Fixture Type _____

35W 120V Xenon Lamps with **with SPEED&LINK™**



Dimensions	Lamps	White - WT	Bronze - BZ	Satin Aluminum - SA
8" 8"L x 3 5/8"W x 1 1/8"H	1	NMA120L-8WT	NMA120L-8BZ	NMA120L-8SA

35W 120V Xenon Lamps no transformers

Lamp 120V: L-35
35W Xenon Type JCD, G-8 Base Clear, 270 lumens, 2900°K
Finish WT-White, BZ- Bronze, SA-Satin Aluminum

MACH 120® FEATURES

- **Three power options** – **Hardwire** through knockouts, **Interconnected** with SpeedLink™ technology or **Portable** with cord and plug option
- **35W/120V Long-life Xenon lamps** included
- Optional **Master Switch** allows single switch control of a run of Mach 120 when a wall switch is not available
- 120V Long-life xenon lamps – **20 Lamps** with one power feed when linking.
- Fast easy installation – furnished complete with mounting hardware
- Internal connectors allow instant hardwiring without wire nuts
- Knockouts on back for Romex, flex or rigid conduit - 1/2" MC connector included with each fixture
- Extruded aluminum construction
- Porcelain Sockets used for high temperature tolerance
- Glass prismatic diffuser for maximum light distribution
- Hinged glass door – no tools required for relamping
- Hi-Off-Lo switch, dimmable, energy saving
- **Multiple US patents pending**



SPEED&LINK™



Master Switch module (NMS-1) controls a run of Mach 120 with a single switch.

