

## 557-00112

The HellermannTyton portable sign printer is designed to print a wide variety of signs and pipe markers for use in industrial, alternative energy, MRO and control panel applications. A wide variety of colored vinyl tapes and printing ribbons allow custom designed signs to be easily created and printed. The printer comes with a cutting blade that cuts the vinyl to length at the end of each print job. Each printer is supplied with the most common electrical pictograms and symbols. Signs up to 2" wide can be printed.

<b>Part No.</b>	557-00112
<b>Type</b>	OSPLP
<b>Material</b>	Plastic
<b>Halogenfree</b>	YES
<b>Material Specification</b>	HF
<b>ROHS Conformity</b>	 RoHS
<b>Color</b>	Gray (GY)
<b>Pkg. Qty.</b>	1 / 1
<b>EAN code</b>	4031026446851



### Features

Rechargeable battery with a low discharge rate for long term use, Soft key menu for easy navigation, Large LCD screen 2.62" X 1.31" (256 X 128 pixel) allows up to 5 lines of text to be displayed in high resolution, A precision cutter lever for clean, crisp label edges, Lightweight design (2.7 lbs, 1.22kg) fits in the palm of your hand and is easy to handle for long periods, Rugged design exterior stands up to industrial use, High quality 203 dpi print head for high resolution printing

