

JCV

- Only for Use in Approved Enclosed Halogen Fixtures
- Minican Screw Base - E10/E11
- Mogul Screw Base - E39
- Universal Burn Position



Watts	Ushio Ordering Code	Ushio Lamp Description	Dimensions mm			Filament Type	Approx Lumens lm	Color Temp K	Avg Life h	Bulb Finish
			Dia (A)	MOL (B)	LCL (C)					
Mini Candelabra Base – E10										
150	1000479	FBT, JCV30V-150W*	11.5	60.0	27.5	CC-8	5000	3400	6	Clear
250	1000480	FBV, JCV30V-250WS*	11.5	60.0	27.5	CC-8	7850	3400	6	Clear
Mini Candelabra Base - E11										
75	1000988	JCV120V-75WGSN	12.0	69.0	32.0	CC-8	1125	2800	1000	Clear
75	1000989	JCV120V-75WGSNF	12.0	65.0	32.0	CC-8	1170	2850	1000	Frosted
100	1000970	JCV120V-100WGSN	14.0	69.0	32.0	CC-8	1600	2850	1000	Clear
100	1000971	JCV120V-100WGSNF	14.0	69.0	32.0	CC-8	1550	2800	2000	Frosted
100	1000361	ESN, JCV120V-100WGSN2	13.0	71.0	35.0	CC-2V	1800	2850	750	Clear
150	1000377	ETG, JCV120V-150WGSN	13.0	71.0	35.0	CC-8	2800	2900	2000	Clear
150	1000378	ETH, JCV120V-150WGSNF	13.0	71.0	35.0	CC-8	2700	2900	2000	Frosted
150	1000359	ESL, JCV120V-150WGSN2	13.0	71.0	35.0	CC-2V	2800	2900	1000	Clear
250	1000294	EHT, JCV120V-250WGSN	13.5	80.0	41.3	CC-8	5000	3000	2000	Clear
250	1000360	ESM, JCV120V-250WGSNF	13.0	80.0	41.0	CC-8	4800	3000	2000	Frosted
250	1000991	JCV130V-250WGSN	13.0	80.0	41.0	CC-8	5000	3000	2000	Clear
250	1001809	JCV130V-250WGSNF	13.0	80.0	41.0	CC-8	4850	3000	2000	Frosted
300	1000961	JCV100V-300WGS*	15.0	78.0	42.0	CC-8	4650	2850	3000	Clear
300	1001813	JCV120V-300WGS*	15.0	78.0	42.0	CC-8	4650	2950	1500	Clear
325	1000295	EHV, JCV120V-325WBS	13.0	80.0	41.0	CC-8	7800	3100	500	Clear
400	1000976	JCV120V-400WGSN	13.0	92.0	51.0	CC-8	8250	2950	2000	Clear
400	1000977	JCV120V-400WGSNF	13.0	92.0	51.0	CC-8	7850	2950	2000	Frosted
500	1000384	EVR, JCV120V-500WGS	13.0	92.0	51.0	CC-8	10450	2950	2000	Clear
500	1000466	EYX, JCV120V-500WGSF	13.0	92.0	51.0	CC-8	9500	3000	2000	Frosted
500	1000465	EYW, JCV130V-500WGS	13.0	92.0	51.0	CC-8	10000	3000	2000	Clear
500	1000464	EYV, JCV130V-500WGSF	13.0	92.0	51.0	CC-8	9500	3000	2000	Frosted
500	1000995	JCV230V-500WGS*	13.0	92.0	50.8	CC-8	9000	2950	2000	Clear
750	1000463	EYT, JCV120V-750WB1	13.0	95.0	51.0	CC-8	18500	3050	500	Clear
1000	1000967	JCV120V-1000WC3*	13.5	100.0	51.0	CC-8	26000	3200	300	Clear
Mogul Screw Base – E39										
2000	1000095	BWF, JCV120V-2000W	25.0	190.5	133.4	CC-8	59000	3200	500	Clear
2000	1000096	BWG, JCV120V-2000W*	25.0	190.5	133.4	CC-8	57200	3200	500	Frosted

* Special order item

