



Actual

**Catalog Number:** HMC5630-LI  
**Product ID:** 7TAA131540R0013  
**UPC Number:** 78378653048  
**EAN Number:** 05415022359480  
**Status:** Active

6-Ton Lithium-Ion Battery Powered Dieless Open Crimp Tool for Crimping #8-500 kcmil Cu/Al Connectors

- 14.4V lithium-ion battery offers lighter weight, longer run time, no memory effect, minimal discharge and rapid recharge
- Visual indication of complete crimp compression (green/orange/red)
- All tools and batteries come with a standard 5-year warranty
- Covers a wide range of applications in both the electrical and utility markets
- Dieless tool with a 180 degree rotating head, used to compress Homac/Anderson style lugs with 6 tons of force

### North American Specifications (UNSPSC)

UNSPSC	27112750 Battery powered crimping tool
IGCC	2388 Battery powered crimping tool
Brand Name	Blackburn
Type	Battery Power Crimp Tool
Special Features	14.4V lithium-ion battery offers lighter weight, longer run time, no memory effect, minimal discharge and rapid recharge

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	6.25x4.5x12.87
Weight Uom	26.91 lbs. Each

### Documents / Support Tools

Technical Data Sheet Global	wsd-001155
Instruction Sheet 1	ta04742-tb2
Instruction Sheet 2	ta04683-tb2

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com