

Auto Fire Extinguisher

Part number 21006287

Regular use

Disposable

UL Rated 5-B:C



Description

Suitable for use on Class B (liquids & gases) and Class C fires (energized electrical equipment).

The Auto unit is fitted with a pressure gauge that provides at-a-glance status, is manufactured from lightweight aluminum and a tough nylon valve assembly.

Features

- Easy-to-read gauge tells you fire extinguisher is charged and ready for use
- Clear instruction label using graphics to show steps required to operate extinguisher
- Easy-to-pull safety pin
- Rust and impact resistant nylon handle
- 2 lb. of fire extinguishing agent (Average)
- 6 year limited warranty
- UL approved strap retention bracket

At a Glance

- Model Auto FX5 II
- Regular Dry Chemical
- UL listed
- UL rated 5-B:C
- U.S.C.G, DOT approved
- Supplied with retention strap bracket
- Sodium Bicarbonate
- 6 year limited warranty
- Suitable for use on liquid & energized electrical fires

For use on the following types of fire:



Pt # 21006287 - 4 pack
 UPC: 0-47871-06223-2
 IZF: 20047871062236
 Pt # 21006642 - 6 pack
 UPC: 0-47871-06223-2
 IZF: 10047871062239

Product Specification

Net agent weight (Average)	2 lb.
Unit weight (Average)	2.85 lb.
Diameter	3.25 inches
Height	10.95 inches
Discharge time	8-12 seconds
Discharge range	4-6 feet
Operating pressure	100 psi
Cylinder	Seamless aluminum
Valve, handle, lever	Nylon
Strap Bracket	U.S.C.G approved

Packaging Options



MASTER PACK

Packaging dimensions (inches)

	Depth	Width	Height
Carton	3.37	4.25	11.25
Pack (4)	9.1	11.75	7
Pack (6)	9.1	11.75	10