



Dependable Power for Any Application

Product Datasheet

Copper Windings - 240 X 480 Primary Volts - 120/240
Secondary Volts - Four Windings - 1Ø
Dry Type Distribution Transformer - Single Phase

Catalog #: TPC530203S



PRODUCT FEATURES

- UL listed, CSA certified
- Meet DOE 2016 efficiency requirements
- UL Type 3R with optional Weather Shield
- Floor Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

DOE

- Meet or exceed U.S. DOE 10 CFR Part 431

UL STANDARD

- UL 506

CSA STANDARD

- C22.2 No. 47

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

WARRANTY

GENERAL PRODUCT INFORMATION

KVA:	50.00
Primary Voltage:	240 X 480
Secondary Voltage:	120/240
Frequency:	60 Hz
ANFC Taps:	2
BNFC Taps:	4
Taps % Steps:	2.5%
Max Temperature Rise:	150°C
UL Insulation Class:	220°C

PRODUCT MEASUREMENTS

Height (In./cm):	25.50 (64.8)
Width (In./cm):	24.39 (61.9)
Depth (In./cm):	19.37 (49.2)

CONFIGURATION

Construction Type:	Ventilated
Mounting Type:	Floor
Weather Shield:	WSA1
Wiring Diagram:	5

PACKAGING

Ship Weight (Lbs/Kg):	378 (172.0)
-----------------------	-------------

COMPLIANCES

DOE:	Meet or exceed U.S. DOE 10 CFR Part 431
UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No. 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card
	www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf