

Horns

Electronic

Titan Class



The Titan Class are low current, high performance, high decibel audible signals designed for hazardous locations. They can be mounted on any surface using three bolts. Flying leads allow for quick installation.

The 5522MD is diode polarized and primarily intended for use in hazardous location applications requiring electrical supervision of signaling circuit field wiring. These signals may also be used for unsupervised signaling applications.

Features and Specifications

- Corrosion resistant electrostatic heat flowed powder epoxy gray finish
- Fitted with factory sealed 1/2" (13mm) threaded pipe nipple for quick installation
- Diode polarized versions for supervised circuits
- Speaker swivels 180° vertically or horizontally depending on orientation of mounting bracket **(5522MD-AW)**
- 30" (762mm) wire leads
- Horn frequency - 982 Hz
- UL listed for Class I, Div. 1 and 2, Groups B, C and D

Ordering Information

Description	Cat. No.	Operating Voltage ¹	Current	dB at 1m/10ft.
Horn	5522M-AQ	24V DC	0.25 A	119/109
		24V AC	0.95 A	
	5522M-Y6	120-240V AC	0.260 A	119/109
		125-250V DC	0.130 A	
Horn, Diode Polarized	5522MD-AW	24V DC	0.950 A	119/109

¹AC voltage frequency is 50/60 Hz.

Weights and Dimensions

Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)
5522M-AQ	16.50	23.50
5522M-Y6	16.50	23.50
5522MD-AW	16.50	23.50

