

## Low Voltage Industrial Push Buttons

### Panel Mount

### 690 Series

#### FEATURES


- > AC or DC up to 50 volts
- > Polished, anodized aluminum shell
- > Snap fit or locknut type mounting

Low voltage, panel mount push buttons with three types of centers: recessed, flush, or protruding. Each button has a phosphor bronze contact spring with a long duration wiping action. The button back is constructed of Zytel 101 nylon.


Used for push button panels, on industrial and commercial machines, and on OEM equipment. Use wherever an extra long life, high quality, low voltage push button is needed. May be used with Cat. No. 147-1 mounting plate (page 10-11).

#### SPECIFICATIONS

- > Contact ratings:  
12V: 10 amps AC, 4 amps DC  
24V: 10 amps AC, 2 amps DC  
48V: 5 amps AC, 1 amp DC
- > Mounting hole dia: 5/8" (16mm)
- > Normally open momentary contacts



Cat No. 694-B,  
694-W, 695-B, and 695-W



Cat No. 690-W,  
692-W, and 691-W

Cat. No.	Center Mounting	Center Type	Color
690-W	Snap fit	Flush	White
691-W	Locknut	Flush	White
692-W	Snap fit	Recessed	White
694-B	Snap fit	Protruding	Black
694-W	Snap fit	Protruding	White
691-W	Locknut	Flush	White
695-B	Locknut	Protruding	Black
695-W	Locknut	Protruding	White

D-04