

Bells

Vibrating

740 and 744

Edwards 740 and 744 bells with an exposed gong are non-adjustable, and are suitable for use in residential, commercial and OEM applications. They may be operated off of a 591 or 592 transformer or DC power. They are also suitable for AC powered security systems with a battery standby.

Features and Specifications

- Exposed gong
- Attractive snap-on covers
- Corrosion resistant chrome finish
- Enclosed binding posts



Ordering Information

Description	Cat. No.	Operating Voltage	Current	VA	dB at 1m/10ft.	DC Coil Res (Ohms)
Non Adjustable, Vibrating	740	6-8V AC 3-6V DC	1.0 A max	7.0	100/90	1.5
	744	6-8V AC 3-6V DC	1.0 A max	10.0	100/90	1.5

Weights and Dimensions

Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)	Dimensions		
			A	B	C
740	0.40	0.42	2 1/2" (64mm)	1 1/4" (32mm)	5 3/4" (146mm)
744	0.52	0.58	4" (102mm)	1 3/4" (44mm)	6 7/8" (175mm)

