

Pulse Start Metal Halide

| Catalog Number | Wattage | Voltage | Overall Length | Case Length | Mount Dim |
|----------------|---------|------------|----------------|-------------|-----------|
| 1120-251A-TC | 35/39 | 120 | 9.50 | 8.35 | 8.85 |
| 11210-236C-TC | 50 | 120 or 277 | 11.75 | 10.56 | 11.14 |
| 11210-277C-TC* | 70 | 120 or 277 | 11.75 | 10.56 | 11.14 |
| 11210-506C-TC* | 70 | 120 or 277 | 11.75 | 10.56 | 11.14 |
| 11210-554C-TC | 70 | 120 or 347 | 11.75 | 10.56 | 11.14 |
| 11210-239C-TC | 100 | 120 or 277 | 11.75 | 10.56 | 11.14 |
| 11210-606C-TC | 100 | 120 or 347 | 11.75 | 10.56 | 11.14 |
| 11210-242C-TC* | 150 | 120 or 277 | 14.31 | 13.19 | 13.75 |
| 11210-539C-TC | 150 | 120 or 277 | 14.31 | 13.19 | 13.75 |

*Double ended lamps (70W M85 & 150W M81)

High Pressure Sodium

| Catalog Number | Wattage | Voltage | Overall Length | Case Length | Mount Dim |
|----------------|---------|------------|----------------|-------------|-----------|
| 12210-261C-TC | 35 | 120 or 277 | 11.75 | 10.55 | 11.10 |
| 12210-236C-TC | 50 | 120 or 277 | 11.75 | 10.55 | 11.10 |
| 12210-237C-TC | 70 | 120 or 277 | 11.75 | 10.56 | 11.14 |
| 12210-552C-TC | 70 | 120 or 347 | 11.75 | 10.55 | 11.10 |
| 12210-239C-TC | 100 | 120 or 277 | 11.75 | 10.55 | 11.10 |
| 12210-606C-TC | 100 | 120 or 347 | 11.75 | 10.55 | 11.10 |
| 12210-241C-TC | 150 | 120 or 277 | 14.30 | 13.15 | 13.75 |
| 12210-602C-TC | 150 | 120 or 347 | 14.30 | 13.15 | 13.75 |



Multi-5[®] Uni-Pak The Complete HID Solution

Universal's Multi-5 Uni-Pak ballast and lamp replacement kits offer all the benefits of the distributor kit with the addition of a lamp.

- Includes the ballast, lamp and all components and hardware needed for fast and accurate ballast replacement.

| Catalog Number | Description | Length | Height | Width | Weight |
|------------------|--|--------|--------|-------|--------|
| M175ML5AC3M555K | 175W MH M57 Multi-5™ Ballast & M57 Lamp Kit | 11.5 | 10.0 | 5.0 | 9.0 |
| M250ML5AC3M555K | 250W MH M58 Multi-5™ Ballast & M58 Lamp Kit | 12.1 | 6.8 | 12.1 | 11.8 |
| M250ML5AC4M555K | 250W MH M58 Multi-5™ Ballast & M58 Lamp Kit | 12.1 | 6.8 | 12.1 | 14.1 |
| M400ML5AC4M555K | 400W MH M59 Multi-5™ Ballast & M59 Lamp Kit | 12.6 | 6.6 | 14.0 | 14.7 |
| M1000ML5AC5M555K | 1000W MH M47 Multi-5™ Ballast & M47 Lamp Kit | 18.0 | 17.0 | 8.5 | 25.1 |
| P250ML5AC4L555K | 250W PSMH M153 Multi-5 Ballast & M153 Lamp Kit | 12.1 | 6.8 | 12.1 | 13.0 |
| P320ML5AC4L555K | 320W PSMH M154 Multi-5 Ballast & M154 Lamp Kit | 12.6 | 6.6 | 14.0 | 14.7 |
| P400ML5AC4L555K | 400W PSMH M155 Multi-5 Ballast & M155 Lamp Kit | 12.6 | 6.6 | 14.0 | 14.7 |
| P750ML5AC5M555K | 750W PSMH M149 Multi-5 Ballast & M149 Lamp Kit | 18.0 | 17.0 | 8.5 | 20.5 |
| S250ML5AC40555K | 250W HPS S50 Multi-5™ Ballast & S50 Lamp Kit | 12.1 | 6.8 | 12.1 | 11.0 |
| S400ML5AC4M555K | 400W HPS S51 Multi-5™ Ballast & S51 Lamp Kit | 12.1 | 6.8 | 12.1 | 18.1 |
| S1000ML5AC5M555K | 1000W HPS S52 Multi-5™ Ballast & S52 Lamp Kit | 18.0 | 17.0 | 8.5 | 26.0 |