



Actual

Catalog Number: TBM62CR-LI
Product ID: 7TAA131540R0011
UPC Number: 78378653038
EAN Number: 05415022360813
Status: Active

6-Ton Lithium-Ion Battery Powered Inline Closed Crimp Tool for Crimping #8-600 kcmil Cu, #8-400 kcmil Al Connectors

- 14.4V lithium-ion battery offers lighter weight, longer run time, no memory effect, minimal discharge and rapid recharge
- Visual indication of complete crimp compression (green/orange/red)
- All tools and batteries come with a standard 5-year warranty
- Covers a wide range of applications in both the electrical and utility markets
- Designed with rotating 180 degree jaws and integrated LED work lights offering more maneuverability in tight spaces, while still providing 6 tons of parallel action crimping force

North American Specifications (UNSPSC)

UNSPSC	27112750 Battery powered crimping tool
IGCC	2388 Battery powered crimping tool
Brand Name	Blackburn
Type	Battery Power Crimp Tool
Special Features	14.4V lithium-ion battery offers lighter weight, longer run time, no memory effect, minimal discharge and rapid recharge
Crimping Force	6 Tons
Battery	Lithium Ion

Packaging

Outer Quantity	1
Outer Dimensions (inches)	6.25x4.5x12.87
Weight Uom	20.83 lbs. Each

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-001152
Instruction Sheet 1	ta04713-tb2
Instruction Sheet 2	ta04683-tb2

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com