

# XENON Bi-Pin Lamps

WAC LIGHTING  
Responsible Lighting®



**BP-50-12V**

Fixture Type:

Catalog Number:

Project: \_\_\_\_\_

Location: \_\_\_\_\_



**BP-10-12V, BP-20-12V**



**JCD-20X-CL**

## Low Voltage Bi-pin – Quick Connect™ Pendants, Sconces

Model	Power	Color Temp	Volt	Lumens	Average Life	Base	Length
<b>BP-50-12V</b>	50W	3000K	12V	600	10,000 Hours	GY6.35	1 <sup>15</sup> / <sub>16</sub> "

## Low Voltage Bi-pin – Button Lights

<b>BP-10-12V</b>	10W	3000K	12V	100	10,000 Hours	G4	1 <sup>1</sup> / <sub>4</sub> "
<b>BP-20-12V</b>	20W	3000K	12V	200	10,000 Hours	G4	1 <sup>1</sup> / <sub>4</sub> "

## Line Voltage Bi-pin – Xenon Light Bars

<b>JCD-20X-CL</b>	20W	3000K	12V	300	7,000 Hours	G8-0	1 <sup>1</sup> / <sub>2</sub> "
-------------------	-----	-------	-----	-----	-------------	------	---------------------------------

## ORDER NUMBER

-

Example: **BP-20-12V**

WAC Lighting  
www.waclighting.com  
Phone (800) 526.2588 • Fax (800) 526.2585

Headquarters/Eastern Distribution Center  
44 Harbor Park Drive • Port Washington, NY 11050  
Phone (516) 515.5000 • Fax (516) 515.5050

Western Distribution Center  
1750 Archibald Avenue • Ontario, CA 91760  
Phone (800) 526.2588 • Fax (800) 526.2585