



Actual

Catalog Number: **STC1102**
Product ID: 7TAH006710R0028
UPC Number: 78378613424
EAN Number: 05415022245004
Status: Active

Type STC - Copper Single-Conductor, One-Hole Mount (Straight Tang), Conductor Range 2 Str-1/0 Str, Length 1-15/16 Inches, Width 5/8 Inch, Height 1-1/4 Inches

- Uniquely designed pressure bar and notched v-bottom collar provide vise-like grip between conductor and terminal.
- Made of electrolytic seamless copper. Screws are zinc-plated steel.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Copper Connectors
Special Features	Uniquely designed pressure bar and notched v-bottom collar provide vise-like grip between conductor and terminal.
Standard	UL E9809
Material	Copper
Conductor Range (Main/Primary)	2 Str-1/0 Str

Packaging

Inner Quantity	10
Inner Dimensions (inches)	3.7x3.3x3.3
Outer Quantity	180
Weight Uom	10.56 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com