



GROUP F – 316 SS

316 STAINLESS STEEL ENCAPSULATED TRANSFORMERS, 115° C RISE 480 DELTA PRIMARY VOLTS — 208Y/120 SECONDARY VOLTS — 3Ø, 60 Hz

kVA	CATALOG NO.	APPROX. DIMENSIONS Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	KNOCKOUTS Inches (Cm.)	WEATHER SHIELD P/N	Wiring Diagrams & Design Figures Begin on Page 154
		HEIGHT	WIDTH	DEPTH					
3.0	T2A53308SS	10.38 (26.4)	12.37 (31.4)	7.47 (19.0)	75 (34.0)	W	NA	NA	21-F
6.0	T2A53309SS	11.83 (30.0)	14.17 (36.0)	8.82 (22.4)	140 (63.5)	W	NA	NA	21-F
9.0	T2A53310SS	14.03 (35.6)	17.77 (45.1)	11.52 (29.3)	180 (81.6)	W	NA	NA	21-F
15.0	T353311SS	18.86 (47.9)	20.30 (51.6)	9.03 (22.9)	250 (113.0)	F	NA	NA	21-I
30.0	T379312SS	24.81 (63.0)	27.13 (68.9)	11.14 (28.3)	613 (278.1)	F	NA	NA	22-I
45.0	T379313SS	25.31 (64.3)	30.18 (76.7)	12.76 (32.4)	780 (354.0)	F	NA	NA	22-I
75.0	T379314SS	26.82 (68.1)	34.68 (88.1)	15.25 (38.7)	1126 (511.0)	F	NA	NA	22-I

Notes: 3.0 through 75.0 kVA units encapsulated (TP1 exempt)

GROUP G

480 DELTA PRIMARY VOLTS — 240 DELTA / 120 TAP SECONDARY VOLTS MAY BE USED ON A 4 WIRE 480Y/277 VOLT SUPPLY — 3Ø, 60 Hz

kVA [Ⓢ]	CATALOG NO.	APPROX. DIMENSIONS Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	KNOCKOUTS Inches (Cm.)	WEATHER SHIELD P/N	Wiring Diagrams & Design Figures Begin on Page 154
		HEIGHT	WIDTH	DEPTH					
3.0	T2A-533281S	10.38 (26.4)	12.37 (31.4)	7.47 (19.0)	75 (34.0)	W	0.75-1.25 (1.9-3.2)	NA	25-F
6.0	T2A-533291S	11.83 (30.0)	14.17 (36.0)	8.82 (22.4)	140 (63.5)	W	0.75-1.25 (1.9-3.2)	NA	25-F
9.0	T2A-533401S	14.03 (36.0)	17.77 (45.1)	11.52 (29.3)	180 (81.6)	W	0.75-1.25 (1.9-3.2)	NA	25-F
15.0	T3-533411S	18.86 (47.9)	20.30 (51.6)	9.03 (22.9)	250 (113.0)	F ①	NA	NA	25-I
30.0	TP1533423S	25.50 (64.8)	24.39 (61.9)	19.37 (49.2)	325 (147.0)	F ①	NA	WSA1	26-E
45.0	TP1533433S	25.50 (64.8)	24.39 (61.9)	19.37 (49.2)	400 (181.0)	F ①	NA	WSA1	26-E
75.0	TP1533443S	29.41 (74.7)	28.15 (71.5)	22.37 (56.8)	500 (226.8)	F ①	NA	WSA2	26-E
112.5	TP1533453S	35.47 (91.2)	31.90 (81.0)	26.88 (68.3)	750 (340.0)	F	NA	WSA3	26-E
150.0	TP1533463S	41.52 (105.5)	32.90 (83.6)	29.87 (75.9)	1125 (510.0)	F	NA	WSA4	26-E
225.0	TP1533473S	41.52 (105.5)	32.90 (83.6)	29.87 (75.9)	1200 (544.0)	F	NA	WSA4	26-E
300.0	TP1533483S	45.60 (115.8)	39.50 (100.3)	35.50 (90.2)	1550 (703.0)	F	NA	WSA5	26-G
500.0	TP1533493S	62.00 (157.5)	54.00 (137.2)	42.00 (106.7)	2675 (1213.0)	F	NA	WSA7	26-G
750.0	TP1533503S	62.80 (159.5)	54.00 (137.2)	41.50 (105.4)	3408 (1545.8)	F	NA	WSA6	26-G

Notes: 3.0 through 15.0 kVA units encapsulated (TP1 exempt), 30.0 through 750.0 kVA TP1 compliant. 3.0 kVA through 750.0 kVA provided with 120V lighting tap limited to 5% of nameplate rating.

GROUP G2

LOW NOISE (minus 3 db) 480 DELTA PRIMARY VOLTS — 240 DELTA / 120 TAP SECONDARY VOLTS MAY BE USED ON A 4 WIRE 480Y/277 VOLT SUPPLY — 3Ø, 60 Hz

kVA	CATALOG NO.	APPROX. DIMENSIONS Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	KNOCKOUTS Inches (Cm.)	WEATHER SHIELD P/N	Wiring Diagrams & Design Figures Begin on Page 154
		HEIGHT	WIDTH	DEPTH					
30.0	LN3533423S	29.48 (74.9)	28.15 (71.5)	22.37 (56.8)	360 (163.3)	F ①	NA	WSA2	26-E
45.0	LN3533433S	29.48 (74.9)	28.15 (71.5)	22.37 (56.8)	417 (189.2)	F ①	NA	WSA2	26-E
75.0	LN3533443S	35.47 (90.1)	31.90 (81.0)	26.88 (68.3)	536 (243.1)	F ①	NA	WSA3	26-E
112.5	LN3533453S	41.50 (105.4)	32.90 (83.6)	29.90 (75.9)	800 (362.9)	F	NA	WSA4	26-E
150.0	LN3533463S	41.50 (105.4)	32.90 (83.6)	29.90 (75.9)	950 (430.9)	F	NA	WSA4	26-E
225.0	LN3533473S	41.50 (105.4)	32.90 (83.6)	29.90 (75.9)	1256 (569.7)	F	NA	WSA4	26-E

Notes: 30.0 through 225.0 kVA TP1 compliant

① Wall mounting brackets are available for these sizes, refer to page 165.