



Dependable Power for Any Application

Product Datasheet

240 X 480 Primary Volts - 24/48 Secondary Volts - 1Ø Buck-Boost Transformer - Single Phase

Catalog #: T243570



PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Single or Three Phase Applications
- Wall Mounted
- Covered under Acme's 10 year limited warranty

BENEFITS

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in kVA

UL STANDARD

UL 506

CSA STANDARD

C22.2 No 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

VA: -
kVA: 7.50

| | |
|-----------------------|-----------|
| Primary Voltage: | 240 X 480 |
| Secondary Voltage: | 24/48 |
| Frequency: | 60 Hz |
| Max Temperature Rise: | 115°C |
| UL Insulation Class: | 180°C |

PRODUCT MEASUREMENTS

| | |
|------------------|--------------|
| Height (In./cm): | 20.81 (52.9) |
| Width (In./cm): | 11.12 (28.2) |
| Depth (In./cm): | 10.84 (27.5) |

CONFIGURATION

| | |
|--------------------|--------------|
| Construction Type: | Encapsulated |
| Mounting Type: | Wall |

PACKAGING

| | |
|-----------------------|------------|
| Ship Weight (Lbs/Kg): | 125 (56.7) |
|-----------------------|------------|

COMPLIANCES

| | |
|---------------|--|
| UL Standard: | UL 506 |
| UL Listed: | File E79947 |
| CSA Standard: | C22.2 No 47 |
| CSA Listed: | LR7357-32 |
| Warranty: | Acme Electric Warranty Card |
| | www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf |