



Actual

Catalog Number: 1000HPS
Product ID: 7TAH006110R0000
UPC Number: 78378620052
Status: Active

Type HPS - Split-Bolt Connector with Spacer, Conductor Range for Equal Main and Tap AC-SR 900-477, Conductor Range for Equal Main and Tap 1000 kcmil-500 kcmil, Min Tap with One Max Main 4/0 Str, Tin Plated

- Bolt and pressure bar of copper alloy, completely tin plated for corrosion resistance. Contoured spacer of bronze alloy copper.
- Splicing, tapping or terminating conductors in power and grounding electrical connection.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Split-Bolt
Special Features	Bolt and pressure bar of copper alloy, completely tin plated for corrosion resistance. Contoured spacer of bronze alloy copper.
Application	Splicing, tapping or terminating conductors in power and grounding electrical connection.
Standard	UL E9809
Material	Copper Alloy
Finish	Electro Tin-Plated
Color	Metallic

European Specifications (ETIM)

ETIM	EC000491 Earth terminal clamp
Suitable for	Round conductor
Material	Copper

Packaging

Inner Quantity	1
Inner Dimensions (inches)	4.09x3.03x2.72
Outer Quantity	18
Outer Dimensions (inches)	11x9.8x8
Weight Uom	2.9 lbs. Each

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000072

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com