



Actual

Catalog Number: ADR21AR
Product ID: 7TAH006600R0203
UPC Number: 78378614983
EAN Number: 05415022398205
Status: Active

Type ADR-ALCUL Anti-Rotational Single-Conductor, One-Hole Mount, Conductor Range Max 2/0 Str, Min 14 AWG, 1/4 Inch Bolt Hole, Tin Plated

- Unique bottom rib keeps the conductor from turning. Eliminates the need for excessive torque, which can damage large conductors.
- Bottom rib prevents conductor from loosening, even in heavy-vibration applications.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Anti-Rotational Mechanical Connector
Special Features	Unique bottom rib keeps the conductor from turning. Eliminates the need for excessive torque, which can damage large conductors.
Standard	UL E9809
Number Of Conductors	1
Material	Aluminum
Finish	Tin-Plated
Conductor Range (Main/Primary)	14-2/0
Number Of Mounting Holes	1
Mounting Hole Spacing	1/4 Inch

Packaging

Inner Quantity	25
Inner Dimensions (inches)	4.2x3.1x2.8
Outer Quantity	250
Outer Dimensions (inches)	15x7x4.75
Weight Uom	3.19 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com