



Representative

**Catalog Number:** KL31-1  
**Product ID:** 7TAA267190R0034  
**UPC Number:** 78378604753  
**Status:** Active

Aluminum 3-1/2 Inch Service Entrance Compression Splice for Wire Range - End A: 2 AS-CR, 1 Sol. Al., 1 Str., 1/0 Str. Compact, Red, End B: 1 Sol. Al., 1 Str., 1/0 Str. Compact, Red, Die: 840

### North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Service Entrance Connectors
Special Features	Splices large conductors required for commercial service, use as low cost reducing sleeve. All sizes can be installed with popular mechanical and hydraulic tools. Center stop assures proper conductor positioning. Quick identifications with color-coded foil caps.
Application	For Combinations of Aluminum-to-Aluminum and Aluminum-to-Copper Conductors
Standard	Passes the requirements of ANSI C119.4
Size	3-1/2 Inch
Connection	Crimp/ Compression
Conductor Range	End A: 2 ASCR, 1 Solid. Al, 1 Stranded, 1/0 Stranded. Compact, End B: 1 Solid. Al, 1 Stranded, 1/0 Stranded. Compact
Number Of Conductors	2
Material	Aluminum
Insulation	None
Mounting	None
Environmental Conditions	All Seasons / Conditions

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	6.75x5.25x3.7
Outer Quantity	250
Outer Dimensions (inches)	21x12.5x8
Weight Uom	26 lbs. per 100

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)