



Dependable Power for Any Application

# Product Datasheet

## 120 X 240 Primary Volts - 24 Secondary Volts - 1Ø - CE Marked Industrial Control Transformer - Encapsulated

Catalog #: CE010350



### PRODUCT FEATURES

- UL and cUL listed
- CE Marked
- Constructed out of electrical lamination with precision wound coils
- Fully encapsulated core and coil
- Available Fuse Kits and Accessories
- Covered under Acme's 10 year limited warranty

---

### BENEFITS

- Molded terminal blocks with isolation barriers
- Dual labeling for easy product identification
- Heavy gauge steel mounting feet
- Fast wire connection terminal

---

### UL STANDARD

UL 506

---

### CSA STANDARD

C22.2 No 66

---

### WARRANTY

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

### GENERAL PRODUCT INFORMATION

VA:	350
Primary Voltage:	120 X 240
Secondary Voltage:	24
Frequency:	50/60 Hz
Max Temperature Rise:	55°C
UL Insulation Class:	105°C

#### PRODUCT MEASUREMENTS

Height (In./cm):	4.03 (10.2)
Width (In./cm):	5.25 (13.3)
Depth (In./cm):	5.00 (12.7)

#### CONFIGURATION

Mounting Type:	Floor
Wiring Diagram:	CE01

#### PACKAGING

Ship Weight (Lbs/Kg):	13.0 (5.9)
-----------------------	------------

#### COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No 66
CSA Listed:	LR7357-16
CE:	CE Marked
Warranty:	Acme Electric Warranty Card <a href="http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf">www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf</a>

