



PRODUCTS

SUPPORT

WHERE TO BUY

NEWS & EVENTS

COMPANY

Products > Climbing-Equipment > Stepladders > 6300 Series > 6310 10 ft Type IAA Fiberglass Step Ladder



## 6310 10 ft Type IAA Fiberglass Step Ladder

[Write the first review](#)

Be the first to [ask a question](#).

### Performance Overview

Style	Size	Reach Height	Load Capacity	Type	Performance Rating
Single Sided	10 ft	14 ft	375 lbs	Type IAA Duty Rating	

The 6310 Fiberglass 10 ft Step Ladder is ideal for professional contractors and industrial users. With a duty rating of 375 pounds, it features a HolsterTop with the Lock-In System to secure tools from falling while keeping them right at hand. The ladder offers a full set of rear horizontals and heavy duty internal spreaders. All steps are knee braced and the foot pads are riveted to the EDGE® structure. The EDGE bracing system helps protect the rail from damage. Each TRACTION-TRED® step is slip resistant and double riveted. Fiberglass rails are non-conductive for working near electricity.

**BUY NOW** ▶



### Resources

[View 6300 Series Page](#)

[Replacement Parts](#)

[Share](#)

[Email page](#) | [Print this page](#)

### Features

- HolsterTop with Lock-In System secures tools to increase productivity
- Shoulder bolt and nut on top hinge
- 4 rivets attach top to each front rail
- Double riveted slip-resistant TRACTION-TRED® steps
- Back-up plates reinforce all top connectors
- Heavy duty internal spreaders
- Full set of rear horizontals spaced one per foot
- All steps and top rear horizontal are knee-braced
- Slip-resistant foot pads attached to the EDGE® structure
- Every rivet backed up by metal, metal plates or washers to protect rails
- Optional manual pail shelf kit, model no. PK76-9 or automatic closing pail shelf kit model no. 76-2
- Plastic railshield

### Accessories



**21-20 Grating Shoes**



**76-2 Molded Plastic**



**AC11 Stepladder**

### Specifications

Feature	Size / Details
Size	10 ft
Reach Height	14 ft
Max. Standing Height	7 ft 8 in
Description of Top Features	Paint tray slot, can hook, Lock in accessory sockets, 2 tool holes, drill hole, p int, quart & gallon paint can, 2 parts trays, tape measure slot



[+ Show more](#)

Edge Bracing	Heavy
Load Capacity	375 lbs
Type	Type IAA Duty Rating
Performance Rating	
Material	Fiberglass
Approx. Width	30-3/8 in
Approx. Spread	65-7/8 in
With Pail Shelf	No
Spreader Material	Steel
Certifications	ANSI A14.5 (2007); OSHA
Approx. Cu. Ft. Per Unit	12.5
Approx. Shipping Wt. Lbs.	39

## Dimensions

Feature	Size
Top Dimension	5-3/4 in x 13 in
Front Rails Dimension	3-1/8 in
Front Flange Dimension	1-3/16 in
Rear Rails Dimension	1-7/8 in
Rear Flange Dimension	1-3/16 in
Steps Dimension	3 in

## Additional 6300 Series Models

Model No.	Size	Reach Height	Max. Standing Height	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit
<a href="#">6303</a>	3 ft	7 ft	1 ft	18-1/8 in	23-1/8 in	2
<a href="#">6304</a>	3 ft	8 ft	1 ft 11 in	19-7/8 in	29 in	3
<a href="#">6305</a>	5 ft	9 ft	2 ft 10 in	21-5/8 in	35-1/8 in	4.1
<a href="#">6306</a>	6 ft	10 ft	3 ft 10 in	23-3/8 in	41-1/4 in	5.3
<a href="#">6307</a>	7 ft	11 ft	4 ft 9 in	25-1/8 in	47-1/2 in	6.6
<a href="#">6308</a>	8 ft	12 ft	5 ft 9 in	26-7/8 in	53-5/8 in	8.1
<a href="#">6310</a>	10 ft	14 ft	7 ft 8 in	30-3/8 in	65-7/8 in	12.5
<a href="#">6312</a>	12 ft	16 ft	9 ft 7 in	33-7/8 in	78-1/4 in	15

## Ratings Summary

Be the first to [write a review](#)

## Product Q&A

(0 Questions · 0 Answers)

---

Be the first to ask a question! [Ask a new question](#)

#### PRODUCTS

- Climbing Equipment
- Fall Protection
- Racks & Ramps
- Featured Products

#### SUPPORT

- Replacement Parts
- Safety Tips
- FAQ
- Literature
- Where to Buy
- Login

#### NEWS & EVENTS

- News Releases
- Featured Videos
- Current Events
- Sponsorships
- Image Library

#### COMPANY

- Profile
- Why Werner
- Innovation
- Locations
- Contact Us
- Legal Notices