



PRODUCTS

SUPPORT

WHERE TO BUY

NEWS & EVENTS

COMPANY

Products > Climbing-Equipment > Extension Ladders > D6300-2 Series > D6320-2 20 ft Type IA Fiberglass D-Rung Extension Ladder



D6320-2 20 ft Type IA Fiberglass D-Rung Extension Ladder

[Write the first review](#)

3 questions | 3 answers [Read all Q&A](#)

Performance Overview

Size	Style	Reach Height	Load Capacity	Type	Performance Rating
20 ft	Multi Section	19 ft	300 lbs	Type IA Duty Rating	

The D6320-2 fiberglass extension ladder has non-conductive rails making this ladder ideal for working near electricity. With a duty rating of 300 pounds, the D6320-2 is durable and long lasting. The exclusive ALFLO® rung joint means TWIST-PROOF® performance on the job. The TRACTION-TRED® D rungs are slip resistant and the side rails are interlocking. The dual action feet are for use on hard or penetrable surfaces and swivel easily. The base and fly sections separate easily to use the base section as a single ladder. The durable rail shield bracket and shoe help protect the bottom of the rail. The fly section rails are pre-pierced at the top for easy field installation of accessories.

Resources

[BUY NOW ▶](#)

[View D6300-2 Series Page](#)

[Replacement Parts](#)

[Share](#)

[Email page](#) | [Print this page](#)

Accessories



74-1 Cable Hook



86-1 Spur Shoe



91-2 Adjustable Pole

[+ Show more](#)

Features

- Exclusive ALFLO® rung joint means TWIST-PROOF® performance
- 1-5/8in Slip-resistant TRACTION-TRED® D-rungs
- Smooth operating pulley with polypropylene rope
- Interlocking Side Rails with internal rail guides on bottom of fly section securely connect rails
- External guides at top of base section securely interlock rails
- Heavy Duty extruded rung locks are spring loaded to operate smoothly
- Pre-pierced holes for easy field installation of accessories
- Base and fly separate easily to use base section as single ladder
- Combination Rail Shield Bracket and Shoe with SHU-LOK® and Slip-Resistant Pad
- Molded Rung Braces on bottom step for increased durability
- Mar-Resistant Molded End Caps

Specifications

Feature	Size / Details
Size	20 ft
Reach Height	19 ft
Max Working Length	17 ft
Extended Length	17 ft

Style	Multi Section
Load Capacity	300 lbs
Type	Type IA Duty Rating
Performance Rating	
Material	Fiberglass
Rung Type	D-Rung
Foot Material	Slip-resistant pad
Number of Sections	2
Base Width	19 in outside shoes
Certifications	ANSI A14.5 (2007); OSHA
Approx. Cu. Ft. Per Unit	8.7
Approx. Shipping Wt. Lbs.	44.5

Dimensions

Feature	Size
Rails Dimension	3-5/16 in
Flange Dimension	1-3/16 in
Rung Dimension	1-5/8 in
Fly Width	16 in

Additional D6300-2 Series Models

Model No.	Size	Reach Height	Max Working Length	Extended Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D6316-2	16 ft	15 ft	13 ft	13 ft	7	36.5
D6320-2	20 ft	19 ft	17 ft	17 ft	8.7	44.5
D6324-2	24 ft	23 ft	21 ft	21 ft	10.3	52
D6328-2	28 ft	27 ft	25 ft	25 ft	12	59.5
D6332-2	32 ft	31 ft	29 ft	29 ft	13.7	71.5
D6336-2	36 ft	34 ft	32 ft	32 ft	15.3	80.5
D6340-2	40 ft	37 ft	35 ft	35 ft	17	88.5

Ratings Summary

Be the first to [write a review](#)

Product Q&A

(3 questions : 3 answers)

Search questions and answers

All

Sort by

PRICE

1 answer

LUCKZ Las Vegas, NV 89108, USA asked this on [D6324-2 24' Type IAA Fiberglass D-Rung Extension Ladder](#)

How to reseal the fiberglass

1 answer

James79761 Dallas, TX, USA asked this on [D6328-2 28' Type IAA Fiberglass D-Rung Extension Ladder](#)

Collapsed length

1 answer

Jim Narberth PA asked this on [D6300-2 Series Fiberglass Multi Section Extension Ladders](#)

1 of 1

PRODUCTS

[Climbing Equipment](#)
[Fall Protection](#)
[Racks & Ramps](#)
[Featured Products](#)

SUPPORT

[Replacement Parts](#)
[Safety Tips](#)
[FAQ](#)
[Literature](#)
[Where to Buy](#)
[Login](#)

NEWS & EVENTS

[News Releases](#)
[Featured Videos](#)
[Current Events](#)
[Sponsorships](#)
[Image Library](#)

COMPANY

[Profile](#)
[Why Werner](#)
[Innovation](#)
[Locations](#)
[Contact Us](#)
[Legal Notices](#)