



# 1 IN LADDERS™



Products > Climbing-Equipment > Multi-Purpose Ladders > MT Series > MT-13 13 ft. Type IA Telescoping MultiLadder



## MT-13 13 ft Type IA Telescoping MultiLadder

### Performance Overview

Style	Size	Extension Height	Number of Positions	Type
MT Series Telescoping MultiLadder	13 ft	7 ft to 11 ft	13	Type IA Duty Rating

The MT-13 Telescoping 13 ft MultiLadder is versatile and easy to transport. The adjustable telescoping design allows the ladder to be used in 4 different positions -- Twin Step Ladder, stairway Step Ladder, extension ladder and as 2 scaffold bases. In the Step Ladder mode, this hybrid ladder can be used for one or two person jobs with a duty rating of 300 pounds per side. The feet are slip resistant and the ends of the multi-position ladder are flared for firm support. Smooth curved rails allow for comfortable climbing. With its many uses, this MultiLadder fits all your climbing needs.

### Features

- Smooth curved rails for comfortable climbing
- Hybrid Ladder easily converts to: 1. Twin Step Ladder 2. Stairway Step Ladder 3. Extension ladder 4. 2 Scaffold bases
- Double riveted steps for long lasting durability
- Extra wide flared bottom for firm support
- Slip resistant feet
- Adjustable telescoping design for maximum versatility
- Designed for one or two person jobs
- Size refers to the ANSI definition of length. ANSI code: A14.2-2007 S.2.4

### Specifications

Feature	Size / Details
Size	13 ft
Style	MT Series Telescoping Multi Ladder
Highest Standing Level-Extension Ladder	7 ft 7 in
Highest Standing Level-StepLadder	2 ft 10 in
Extension Height	7 ft to 11 ft
Reach Height-Extension Ladder	14 ft 3 in
Reach Height-Stepladder	9 ft 4 in
Closed Height	45 in
Number of Positions	13
Ladder Width	22-1/8 in
Rung Type	Multi-Directional
Load Capacity	300 lbs
Type	Type IA Duty Rating
Material	Aluminum
Stair Height	3 ft to 5 ft
StepLadder Height	3 ft to 5 ft
Scaffold Height	1 ft 11 in
Approx. Cu. Ft. Per Unit	5.5
Approx. shipping Weight Lbs.	31.5
Performance Rating	★★★★

### Dimensions

Feature	Size
Rails Dimension	2-5/8 in
Flange Dimension	1 in
Rungs Dimension	1 in
Steps Dimension	1 in

### Accessories



AC18MT Platform



AC24 Multipurpose



PK70 1 LevelLok