

Specification Sheet

1/2 Chrome G25 Globe Incandescent Lamp

Order Number **03156**

Specifications

Energy Used (Watts).....	40
Domestic Code.....	40G25/CH
Volts.....	120
Brightness (Lumens)	N/A
Average Rated Hours	750
Life (in years)*	0.7
Dimmable.....	Yes
Filament Type	C9
Light Center Length (LCL)	2 7/8"
Estimated Yearly Energy Cost**	\$4.82
Country of Origin.....	China



Physical Characteristics

Finish	1/2 Chrome
Base.....	Medium
MOL.....	4 3/8"

* Based on 3 hrs./day

** Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

Westinghouse Lighting, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting, a Westinghouse Electric Corporation licensee
 ®, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.

