



Specification Sheet

Commercial Service[®] CA10 Flame Tip Incandescent Lamp

Order Number **03665**

Specifications

Energy Used (Watts).....	40
Domestic Code.....	40CA10/130
Volts.....	130
Brightness (Lumens)	345
Average Rated Hours	2500
Life (in years)*	2.3
Filament Type	CC2V
Light Center Length (LCL)	2 1/16"
Estimated Yearly Energy Cost**	\$4.82
Country of Origin.....	China



Physical Characteristics

Finish	Clear
Base	Medium
MOL.....	4"

* Based on 3 hrs./day

** Based on 3 hrs./day 11¢/k/Wh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

Westinghouse Lighting, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting, a Westinghouse Electric Corporation licensee
©, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.

