



Specification Sheet

T8 Specialty Incandescent Lamp

Order Number **03892**

Specifications

Energy Used (Watts).....	40
Domestic Code.....	40T8/130
Volts.....	130
Brightness (Lumens)	300
Average Rated Hours	3500
Life (in years)*	3.2
Dimmable.....	Yes
Filament Type	C8
Light Center Length (LCL)	5 3/4"
Estimated Yearly Energy Cost**	\$4.82
Country of Origin.....	China

Physical Characteristics

Finish	Clear
Base	Medium
MOL.....	11 1/2"



* Based on 3 hrs./day

** Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com

Westinghouse Lighting Corporation, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting Corporation, a Westinghouse Electric Corporation licensee
©“Westinghouse” and “You can be sure...if it’s Westinghouse” are all registered trademarks of Westinghouse Electric Corporation

