



Specification Sheet

T10 Specialty Incandescent Lamp

Order Number **03897**

Specifications

Energy Used (Watts).....	25
Domestic Code.....	25T10/F/130
Volts.....	130
Brightness (Lumens)	160
Average Rated Hours	2500
Life (in years)*	2.3
Dimmable.....	Yes
Filament Type	CSV
Light Center Length (LCL)	3 5/16"
Estimated Yearly Energy Cost**	\$3.01
Country of Origin.....	China



Physical Characteristics

Finish	Frost
Base	Medium
MOL.....	5 1/8"

* Based on 3 hrs./day

** Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

Westinghouse Lighting, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting, a Westinghouse Electric Corporation licensee
®“Westinghouse” and “You can be sure...if it’s Westinghouse” are all registered trademarks of Westinghouse Electric Corporation.

