



Specification Sheet

Toughshell®

A19 Specialty Incandescent Lamp

Order Number **03951**

Specifications

Energy Used (Watts).....	100
Domestic Code.....	100A/TS/130
Volts.....	130
Brightness (Lumens)	860
Average Rated Hours	4000
Life (in years)*	3.7
Dimmable.....	Yes
Filament Type	CC6
Light Center Length (LCL)	2 3/4"
Estimated Yearly Energy Cost**	\$12.05
Country of Origin.....	China



Physical Characteristics

Finish.....	Toughshell
Base.....	Medium
MOL.....	4 1/8"

* Based on 3 hrs./day

** Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com

Westinghouse Lighting Corporation, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting Corporation, a Westinghouse Electric Corporation licensee
®“Westinghouse” and “You can be sure...if it’s Westinghouse” are all registered trademarks of Westinghouse Electric Corporation

