

## Specification Sheet

# Eco-PAR PLUS Halogen

# PAR30 Short Neck Reflector Incandescent Lamp

Order Number **36846**

## Specifications

Energy Used (Watts).....	60
Incandescent Equivalent Wattage .....	75
Domestic Code.....	60PAR30/H/FL/ECO/PLUS
Volts.....	120
Candle Power.....	1400
Beam Spread .....	30°
Beam Type.....	Flood
Filament Type .....	CC8
Light Appearance (Kelvin) .....	2850
Efficacy (LPW).....	18
Brightness (Lumens) .....	1070
Average Rated Hours .....	2000
Life (in years)* .....	1.8
Dimmable.....	Yes
Estimated Yearly Energy Cost** .....	\$7.23
Country of Origin.....	China



## Physical Characteristics

Base .....	Medium
MOL.....	3 1/2"

\* Based on 3 hrs./day

\*\* Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

Call 1-800-999-2226 or visit [www.westinghouselighting.com](http://www.westinghouselighting.com)

Westinghouse Lighting Corporation, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting Corporation, a Westinghouse Electric Corporation licensee  
 ®“Westinghouse” and “You can be sure...if it's Westinghouse”are all registered trademarks of Westinghouse Electric Corporation

