

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130110-0035](#)  
**Status:** **Active**  
**Description:** Watertite® Wet Location 70W Metal Halide Magnet Mount Area Light Molded, Cord Type 16/3 SJTOW, Cord Length 3.04m (10.0' )

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

**Agency Certification**

UL E174254

**General**

Product Family	Portable Lighting
Series	<a href="#">130110</a>
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Outlet	None
Product Literature Order No	987650-8054
Product Name	Watertite®
Type	Wide Area Lamps
UPC	78678829248
Woodhead	Yes

**Physical**

Cord Length - Primary	3.04m (10.0' )
Cord Length - Secondary	N/A
Depth	215.90mm (8.500")
Duty	Wet Location
Guard Included	No
Guard Type	N/A
Height	215.90mm (8.500")
Length	231.65mm (9.120")
Material - Globe	Clear Polycarbonate
Material - Guard	N/A
Mounting Style	Magnet
Packaging Type	Carton
Socket Construction	N/A

**Electrical**

Bulb Type	Metal Halide - Probe Start
Cord Type - Primary	16/3 SJTOW
Lamp Type	MH70
Lamp Wattage - Maximum	70W
Lumens	5700
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

**Material Info**

Old Part Number 8565-MH



**EU RoHS**

**Not RoHS Compliant**  
**REACH SVHC**  
**Not Reviewed**  
**Low-Halogen Status**  
**Not Reviewed**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**  
 130110Series