



Actual

**Catalog Number:** TBM14CR-LI  
**Product ID:** 7TAA131540R0005  
**UPC Number:** 78378652970  
**EAN Number:** 05415022345087  
**Status:** Active

14-Ton Lithium-Ion Battery Open Crimp Tool for Crimping #8-900 kcmil Cu, #10-750 kcmil Al Connectors

- 14.4V lithium-ion battery offers lighter weight, longer run time, no memory effect, minimal discharge and rapid recharge
- Visual indication of complete crimp compression (green/orange/red)
- All tools and batteries come with a standard 5-year warranty
- Covers a wide range of applications in both the electrical and utility markets
- Installs up to 900 kcmil copper lugs and splices and up to 750 kcmil lugs and splices

### North American Specifications (UNSPSC)

UNSPSC	27112750 Battery powered crimping tool
IGCC	2388 Battery powered crimping tool
Brand Name	Blackburn
Type	Battery Power Crimp Tool
Special Features	14.4V lithium-ion battery offers lighter weight, longer run time, no memory effect, minimal discharge and rapid recharge
Crimping Force	14 Tons
Battery	Lithium Ion

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	6.25x4.5x12.87
Weight Uom	37.3 lbs. Each

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-001148
Instruction Sheet 1	ta04724-tb2
Instruction Sheet 2	ta04683-tb2

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)