



Job Name:

Job Type:

Comments:

Quantity:

9456-12: 12v 60-150w Transformer Hardwire

Dimensions:

Length: 6 1/4"
Width: 2 1/4"
Height: 1 11/16"

Mounting Proc.: N/A



Material List:

1 Transformer - Plastic - Black

Safety Listing:

UL Listed for Dry Locations
 cUL Listed for Dry Locations

12V Transformer/Hardwire Electric Soft Start Curcuitry UL& C-UL Approved W/ Terminal Block For Romax Input & 10/2 AWG Cable Output

Electronic transformers have soft start circuitry which increases lamp life. They emit no audible noise, are UL and C-UL approved, moisture and shock resistant, employ automatically resetting short circuit protection, and are dimmable.

Includes terminal block for 12/2 AWG max. romex input and 10/2 AWG Ambiance® cable output.

UPC #:785652945625

Finish: Black (12)

Shipping Information:

| Package Type | Product # | Quantity | UPC | Length | Width | Height | Cube | Weight | UPS Ship |
|-----------------|-----------|----------|----------------|--------|-------|--------|--------|--------|----------|
| Individual | 9456-12 | 1 | 785652945625 | 6 | 3 | 3 | 0.031 | 0.9 | Yes |
| Master Pack | | 2 | 10785652945622 | 6 | 6 | 6 | 0.125 | 1.95 | Yes |
| Shipping Master | | 32 | 10785652945622 | 25.5 | 13 | 13.75 | 2.638 | 34.2 | Yes |
| NJ Pallet | | 960 | | 48 | 40 | 72 | 80 | 1026 | No |
| NV Pallet | | 960 | | 48 | 40 | 67 | 74.444 | 1026 | No |