

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130111-0044](#)
Status: **Active**
Description: Pro Yellow® Molded Stringlight, 150W, 14/2 SJTW with 2.43m (8.0') Lead 10 Sockets with Guards, Overall Length 30.48m (100.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E112216

General

Product Family	Portable Lighting
Series	130111
Depth	N/A
Height	N/A
Length	30.48m (100.0')
NEMA Configuration	NEMA 1-15
NEMA Rating	Rain Tight
Outlet	None
Product Name	Pro-Yellow®
Type	String Lights
UPC	78172533561
Woodhead	Yes

Physical

Cord Length - Primary	2.43m (8.0')
Cord Length - Secondary	0.61m (2.0')
Duty	Commercial
Guard Included	Yes
Guard Type	N/A
Material - Guard	Polypropylene
Mounting Style	Stringer
Packaging Type	Carton
Socket Construction	Molded

Electrical

Bulb Type	Incandescent
Cord Type - Primary	14/2 SJTW
Lamp Type	A21
Lamp Wattage - Maximum	150W
Lumens	1500
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info

Old Part Number 5030

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130111Series](#)