



Representative

Catalog Number: CU250
Product ID: 7TAH007510R0025
UPC Number: 78378613223
Status: Active

Type CU Copper Splice, Long Barrel, 3-3/8 Inch Length, Max 35kV, Wire Size 250 kcmil, Tin Plated, Die Color Code Yellow

- Made of high-conductivity seamless copper tubing. Tin plated for corrosion resistance.
- Specifically chamfered barrel for ease of installation.
- Color-coded for matching die identification.

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Long Barrel Copper Splice
Special Features	Made of high-conductivity seamless copper tubing. Tin plated for corrosion resistance.
Standard	UL E9809
Conductor Range	250 kcmil
Material	Copper
Finish	Tin Plated
Color	Yellow
Voltage Rating	35KV

European Specifications (ETIM)

ETIM	EC001059 Crimp splices for copper conductor
Sleeve form	Long
Material	Copper
Surface protection	Tinned
Insulation	None
Voltage row	Up to 35kV

Packaging

Inner Quantity	10
Inner Dimensions (inches)	3.5x3x3
Outer Quantity	100
Outer Dimensions (inches)	3.6x3.1x3.1
Weight Uom	17.38 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com